



ENGLISH

Datasheet

Stock No: 221-563

RS Pro HSS 6 → 20mm Cone Cutter, 2mm Max Drilling Thickness



Product Details

HSS Titanium Nitride Coated Cone Cutter

Coating provides high wear resistance

For use on aluminium alloys, sheet metal, plastics and reinforced plastics up to 2mm thick

22mm shank length

Maximum shank diameter 10mm

HSS & HSS TiN, Individual Cutters & Sets

Specifications

Head Size	3 → 14mm
Maximum Drilling Thickness	2mm
Material	HSS
Minimum Head Size	3mm
Maximum Head Size	14mm