



## Datasheet

ENGLISH

Stock No: 485-971

# RS Pro Black Nitrile Rubber Tank Insulation, 14000mm x 1000mm x 13mm



Image representative of range

## Product Details

### Insulation Sheet Class 0

Fully flexible sheet

Especially suitable for larger areas such as storage tanks, grouped pipework, ducting, and areas with difficult access

Available in 2 metre sheets or roll lengths

Temperature range from  $-40^{\circ}\text{C}$  to  $+116^{\circ}\text{C}$  (when adhered to a flat surface, operating temperature should not exceed  $85^{\circ}\text{C}$ )

Compliant with Part L of the April 2006 Building Regulations



ENGLISH

Thermal Conductivity			
Mean Temp. °C	0	+20	+40
W/(m.K)	0.035	0.037	0.040

#### Standards

BS476 Part 7:1997 Class 1  
BS476 Part 6:1989  
BS4370 Part 2:1973  
DIN 53495  
DIN 4109

## Specifications:

Material	Nitrile Rubber
Dimensions	14000 x 1000mm
Thickness	13mm
Thermal Conductivity	0.034 W/mK, 0.036 W/mK, 0.038 W/mK, 0.04 W/mK
Colour	Black
Length	14000mm
Width	1000mm