

Datasheet

Stock No: 512-238

# RS Pro White PTFE Tape for Sealing



## Product Details

### PTFE Thread Seal Tape

A pure polytetrafluoroethylene (PTFE) tape designed for sealing threaded joints thus replacing conventional products. The material is chemically inert and is suitable for use in aggressive environments e.g. where acids, solvents and gases are present. Making it ideal for water, petrol, oxygen and chemicals such as acetone. As well as preventing pressure/fluid loss, it reduces the risk of bi-metallic corrosion in threaded structures e.g. brass screws in aluminium or steel. Supplied in plastic dispenser reels.

### PTFE Tapes

## Specifications

Width	12mm
Thickness	0.075mm
Length	12m
Colour	White
Application	Sealing
Minimum Operating Temperature	-200°C
Maximum Operating Temperature	+260°C
Operating Temperature Range	-200 → +260 °C