


Datasheet

Stock No: 680-921

RS Pro Copper Rod, 24in x 3/4in Diameter



Product Details

Copper HDHC Rod, Bar & Sheet

A high conductivity, corrosion resistant, malleable copper in rod, bar and sheet form.

Chemical analysis:	
Copper	99.90
Lead	0.005
Bismuth	0.001
Tensile Strength:	
Sheet	240N/mm ²
Half Hard	240N/mm ²

Standards

BS2874/C101 (1986), BS EN 12164 CW 004A

Copper & Brass



Specifications

Material	Copper
Form	Rod
Length	24in
Rod Diameter	3/4in
Tensile Strength	240 N/mm ²