



Datasheet

Stock No: 731-372

RS Pro Silicon Heater Mat

ENGLISH



Features:

Heater Mats

Heater mats designed for areas where standard heating methods are difficult to apply. All mats are self adhesive and have etched foil elements embedded into a glass cloth supported rubber compound. These features provided you with a highly robust but flexible product. The range includes standard rectangular or circular mats powered at a range of voltages at various power ratings.

Features and Benefits

- Backing adhesive from Nitto, no loss in performance
- Flexible Silicone with etched foil heating elements
- Fits to irregularly shaped objects
- Operating temperature +200°C (max.)
- 240 V ac type mats have a circular hole in the centre which can accept a bi-metallic thermostat such as stock no. 339 -291
- All units supplied with instruction leaflet



ENGLISH

Caution

Heater mats are not suitable for stand-alone operation.

Multi-Purpose Process Heaters

In order to obtain optimum performance from these products, it is advised that temperature sensing and control elements be used with them.

Specifications:

Mat Shape:	Rectangle
Power Rating:	60 W
Rectangular Mat Size:	200 x 300mm
Peak Temperature:	+300°C
Supply Voltage:	12 V dc