



## Main

Range	Lisse
Product or component type	Dimmer
Device presentation	Complete product
Load type	Incandescent lamp : 400 W 230 V AC halogen lamp :
Colour tint	Matt white
Quantity per set	Set of 1

## Complementary

Device mounting	Wall mounted
Dimmer application	Inductive load Resistive load
[Ue] rated operational voltage	230 V AC 50 Hz
Number of gangs	1 gang
Connections - terminals	Screw terminals
Fixing mode	By screws : M3.5 25 mm
Material	Urea (carbamide) :
Type of packing	Bag
Height	43.6 mm
Width	87 mm
Depth	87 mm
Product weight	0.072 kg

## Environment

standards	BS EN 60669-2-1
IP degree of protection	IP20