

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

LOC

DIST

REVISIONS

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

H

-

P

LTR

DESCRIPTION

DATE

DWN

APVD



A

INITIAL DRAWING

03FEB2015

GSK

BvH



VIEW A

NOTES:

- 1 PACKAGING: ACC. TO TE SPEC. 107-18032
- 2 ELECTRICAL TEST ACCORDING TE SPECIFICATION 108-18857. SHORT-CIRCUIT AND CONTINUITY TEST AT 500V DC, 0.1s
- 3 WIRING SCHEMA ACC. TO TIA/EIA-568-B AS SHOWN IN WIRING SCHEDULE

WIRING SCHEDULE 3

| CAVITY SIDE A | COLOR | CAVITY SIDE B |
|---------------|-------|---------------|
| 1             | WH/OG | 1             |
| 2             | OG    | 2             |
| 3             | WH/GN | 3             |
| 4             | BU    | 4             |
| 5             | WH/BU | 5             |
| 6             | GN    | 6             |
| 7             | WH/BN | 7             |
| 8             | BN    | 8             |

|          |                              |             |
|----------|------------------------------|-------------|
| 10       | HiFlex MultiPurpose 70°C PUR | 2-2205129-6 |
| 5        | HiFlex MultiPurpose 70°C PUR | 2-2205129-5 |
| 3        | HiFlex MultiPurpose 70°C PUR | 2-2205129-4 |
| 2        | HiFlex MultiPurpose 70°C PUR | 2-2205129-3 |
| 1        | HiFlex MultiPurpose 70°C PUR | 2-2205129-2 |
| 0.5      | HiFlex MultiPurpose 70°C PUR | 2-2205129-1 |
| 10       | HI 125°C TPE                 | 1-2205129-6 |
| 5        | HI 125°C TPE                 | 1-2205129-5 |
| 3        | HI 125°C TPE                 | 1-2205129-4 |
| 2        | HI 125°C TPE                 | 1-2205129-3 |
| 1        | HI 125°C TPE                 | 1-2205129-2 |
| 0.5      | HI 125°C TPE                 | 1-2205129-1 |
| 10       | STD 110°C PVC                | 2205129-6   |
| 5        | STD 110°C PVC                | 2205129-5   |
| 3        | STD 110°C PVC                | 2205129-4   |
| 2        | STD 110°C PVC                | 2205129-3   |
| 1        | STD 110°C PVC                | 2205129-2   |
| 0.5      | STD 110°C PVC                | 2205129-1   |
| Length/m | Cable version                | TE PN       |

|  |  |                                   |                                   |                    |
|--|--|-----------------------------------|-----------------------------------|--------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN 03FEB2015<br>SATHISH KUMAR .G | TE Connectivity                   |                    |
| DIMENSIONS: mm                         |  | CHK 03FEB2015<br>B.VELDHOVEN      |                                   |                    |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | APVD 03FEB2015<br>A.VAN ZANDVOORT | NAME<br>CA MINI IO TYPE I PIGTAIL |                    |
|  |  | PRODUCT SPEC<br>108-78955         | RESTRICTED TO                     |                    |
| MATERIAL                               |  | APPLICATION SPEC<br>114-5506      | SIZE<br>A3                        | CAGE CODE<br>00779 |
| FINISH                                 |  | WEIGHT<br>-                       | DRAWING NO<br>C-2205129           | SCALE<br>NTS       |
| CUSTOMER DRAWING                       |  |                                   | SHEET<br>1 OF 1                   | REV<br>A           |