



Datasheet

Stock No: 325-6228

ENGLISH

RS Pro 500 mm Standard Water Pump Pliers Utility with 140mm Jaw Capacity



Product Details

Utility Pliers

- Right angle teeth grip in all directions
- Undercut tongue and groove positioning channel with 3 to 12 different adjustment dependant on size to prevent slipping
- Fastener, eliminates nut and bolt joint failure
- Reinforced edge to minimise stress breakage
- Heat Treated Teeth - Right angle, laser heat treated teeth grip better and last longer
- C1080 Steel – Uses high carbon C1080 steel for superior performance on the job and specially coated for ultimate rust prevention

Specifications:

Maximum Jaw Capacity:	140mm
Adjustment Method:	Standard
Number of Adjustments:	12
Overall Length:	500 mm
Plier Type:	Utility