



Datasheet

Stock No: 326-4623

ENGLISH

RS Pro 316 A4 Stainless Steel Angle



Product Details

316 Stainless Steel Bar and Angle

- Properties C = 0.08 maximum, Ni 12.0, Cr17, Mo2.25
- Bar to EN10088-3/ EN10051
- Related specifications AS2837-1986-316, AISI TYPE 316, ASTM A276-316
- Used particularly in the chemical and allied industries, especially in conditions of pit-type corrosion

Bar, Angle & Key Steel - Grade 316 (A4)

Austenitic stainless steels which are highly resistant to corrosion due to their Molybdenum content. They are non-magnetic and suitable for applications such as photographic, food, chemical and marine equipment.

Specifications:

Material: 316 A4 Stainless Steel
Form: Angle
Length: 2000mm
Width: 25mm
Height: 25mm
Thickness: 3mm