



ENGLISH

Datasheet

RS Pro Standard HSS Cutters, M2 25 mm, Short Cutters

RS Stock no	Part No.	Cutting Diameter
1238480	20AAM12RS	12 mm
1238481	20AAM14RS	14 mm
1238482	20AAM16RS	16 mm
1238483	20AAM18RS	18 mm
1238484	20AAM20RS	20 mm
1238485	20AAM22RS	22 mm
1238486	20AAM24RS	24 mm
1238487	20AAM26RS	26 mm
1238488	20AAM28RS	28 mm
1238489	20AAM30RS	30 mm
1238490	20AAM32RS	32 mm



RS Pro HSS standard cutters are the ideal choice for all your magnetic drilling & cutting applications. Designed for use in fabrication, construction, railways, petrochemical and any other applications when drilling ferrous metal

Features and Benefits

- Accurate, symmetrical, fine finish hole cutting capabilities
- Reduced friction between the HSS core drill and the material
- Time and energy savings