

FIXED BEAM INSPECTION TORCH

A9



Type: Stainless steel inspection LED torch

Operating Modes: On / Off

Luminous Flux: 20 lumens

LED: LED Light Chip

Beam Range: 26 m

Run Time: 11 hours

Batteries Required: 3 x AAAA Alkaline
(included)

Overall Length: 170 mm

Head Diameter: 12 mm

Barrel Diameter: 9.5 mm

Weight: 62 grams (including batteries)

Body Material: Stainless steel casing

