



ENGLISH

Datasheet

RS Pro Grey Cat5e Ethernet Cable, Twisted Pair U/UTP 305m

RS Stock No: **557-464**



Product Details

RS Pro Cat5e cable in grey colour, measures 305 m. This twisted pair cable has U/UTP shield type. It is perfect for enhanced, high performance Cat5e cable for LAN applications or future proofing of structured cabling systems.

Features and Benefits

- Enhanced, high performance Cat5e cable for LAN applications or future proofing of structured cabling systems
- Designed to deliver robust performance and ensure optimum bandwidth
- Supports horizontal networking applications up to 100 m

Specifications:

American Wire Gauge	24 AWG
Attenuation	≥40 dB
Cable Shape	4 Twisted Pair
Capacitance	≤1600 pF/km
Conductor Strand Type	Stranded
Core Strands	1/24 mm
Cross Sectional Area	0.2 mm ²
Length	305 m
Number of Strands	1
Outer Diameter	5 mm
Outer Sheath Material	PVC
Sheath Colour	Grey
Shield Type	U/UTP
Size of Strands	24 AWG
Standards Met	ANSI/TIA 568-C.2, EN 50173, IEC 61156-5, EN 50288-3-1, ISO/IEC 11801 2nd Edition, RoHS Compliant
Conductor Material	Copper
Insulator Material	PE