

Datasheet

RS Pro 71251 Series, 3 Pole Din Connector Socket, DIN 41524, 3A, 34 V, Twist Lock

RS Stock No: 167-3722



Product Details

RS Pro 3-pole DIN connector socket with DIN 41524 has a current rating of 3 A and voltage rating of 34 V. It comes with twist lock.

Features and Benefits

- 1/4 turn locking DIN rail plug
- The housing is protected by nickel-tin galvanising
- Features twist lock

**Specifications:**

Connector Size	Standard
Contact Material	Brass
Contact Plating	Nickel
Current Rating	3 A
DIN Number	DIN 41524
Gender	Female
Housing Material	Metal
Mating Type	Twist Lock
Mounting Type	Through Hole
Number of Contacts	3
Termination Method	Solder
Voltage Rating	34 V
Contact Resistance	<10 mΩ
Insulation Resistance	>10 mΩ