



ENGLISH

Datasheet

PUR 25m Long transparent Flexible Tube Reinforced, 110mm Bend Radius, Applications Various

RS Stock number 339-6310



CPR - 12.5 x 18.5 Refcd PU Clear 25M

Internal Diameter	12.50 mm± 0.25 mm
External Diameter	18.00 mm± 0.50 mm
Length	25 Meter± 1 %
Reinforcement	Braid Material Polyester Type 1 x 1100 Number of Ends 8 Per Side Stitches Per Inch 7.0
Colour	First Tube Colour Clear Second Tube Colour N/A Cover Colour Clear Stripe Colour N/A
Print	R.S. 339 - 6310 (Date Code)
Material	First Tube Material Polyurethane (Ester) Second tube Material N/A Cover Material Polyurethane (Ester) Stripe Material N/A
Packaging	Tied and Film Wrapped
Working Pressure	7 Bar Max @ 20°C
Burst Pressure	21 Bar Min @ 20° C
Safety Factor	3:1
Temperature Range	-40°C to + 65°C
Bend Radius	TBA
Applicable Standards	N/A