



ENGLISH

Datasheet

RS Pro Red Heat Shrink Tubing length 3.7cm ratio 1:1

RS Stock No: **458-0702**



Product Details

RS Pro heat shrink tubing in red colour, has a length of 3.7 cm with 1:1 ratio. The three-colour coded, watertight crimp splices are covered with dual wall heat shrink tubing and hot melt inner liner. The crimp splices offer excellent strain relief, visual inspection, solvent and moisture resistance with good physical and electrical properties.

Features and Benefits

- Voltage rating of 600 V
- Covered with dual wall heat shrink tubing and hot melt inner liner
- Provides superior strain relief, visual inspection, solvent and moisture resistance with good physical and electrical properties



ENGLISH

Specifications:

Adhesive Lined	No
Angle	Straight
Colour	Red
Dielectric Strength	19.7 kV/mm
Maximum Operating Temperature	+125°C
Minimum Operating Temperature	-55°C
Operating Temperature Range	-55 to +125°C
Shrink Ratio	1:1
Sleeve Length	3.7 cm
Sleeve Type	Heat Shrink
Standards Met	RoHS Compliant