

LED360 IP20 – HID Retrofit



Description

This range of IP20 LED lamps are ideal replacements for high intensity discharge lamps (HPS & MH) in open fittings such as low bay and high bay fittings.

Features

- High output Epistar LEDs
- 360° light output – no dark spots
- Ideal as direct replacement for HPS & MH lamps – up to 80% energy saving
- Instant start and restart – can be used with PIR sensors
- E27 & E40 lamp base
- 60W, 80W & 100W versions incorporate a cooling fan in base to aid heat dissipation
- Not suitable for enclosed fittings
- 30,000 hours rated life
- 3 year guarantee

Range

30W LED360 lamp - internal driver	7884628
40W LED360 lamp - internal driver	7884622
60W LED360 lamp - internal driver	7884631
80W LED360 lamp - internal driver	7884634
100W LED360 lamp - internal driver	7884638

Technical Specification

Voltage	100 - 300V~ 50-60Hz
Driver	Integral
Lamp col. temp.	6000k
Lumen	30W 3100lm
Output	40W 4200lm
	60W 6500lm
	80W 9000lm
	100W 12000lm
CRI	≥70
Power factor	≥0.9
Lamp	30W E27
Base	40W – E40
	100W
IP Rating	IP40

Dimensions

	Length	Diameter Ø
30W	194mm	94mm
40W	236mm	94mm
60W	287mm	94mm
80W	270mm	118mm
100W	306mm	118mm