



ENGLISH

Datasheet

RS Pro 1 Phase 4.8kVA Variac, 1 Output, 240V

RS Stock No: **890-2816**



Product Details

RS Pro 1-phase 4.8 kVA variac is a professional range of open style variable transformer available in either single or three phase. This transformer is not designed to provide mains isolation but does not operate at mains voltage. It has a primary voltage of 240 V and a single output. The transformers need to be fitted within an enclosure or a protected environment. This variac meets RoHS compliant.

Features and Benefits

- Single or three phase versions available in a range of current ratings
- Heavy duty construction
- High efficiency & excellent regulation
- No waveform distortion
- Silver plated commutator
- Overload capacity
- Negligible maintenance
- Trouble free long life

**Specifications:**

Construction	Enclosed
Depth	190 mm
Dimensions	225 x 225 x 190 mm
Knob Rotation	Clockwise
Length	225 mm
Maximum Operating Frequency	60 Hz
Minimum Operating Frequency	50 Hz
Mounting Type	Surface
Number of Outputs	1
Number of Phases	1
Power Rating	4800 VA
Primary Current Rating	20 A
Primary Voltage Rating	240 V ac
Protection Features	Overload Protection
Secondary Voltage Rating	0 to 240 V ac, 0 to 270 V ac
Standards Met	RoHS Compliant
Termination Type	Termination Wire
Weight	15.3 kg
Width	225 mm