



ENGLISH

Datasheet

**RS Pro 3 Phase 16.3kVA Variac, 3 Output, 415V**

RS Stock No: **890-2869**



## Product Details

RS Pro 3-phase 16.3 kVA variac is a professional range of open style variable transformer available in either single or three phase. This transformer is not designed to provide mains isolation but does not operate at mains voltage. It has a primary voltage of 415 V and a 3 output. The transformers need to be fitted within an enclosure or a protected environment. This variac meets RoHS compliant.

**Specifications:**

Construction	Enclosed
Depth	445 mm
Dimensions	250 x 300 x 445 mm
Knob Rotation	Clockwise
Length	250 mm
Maximum Operating Frequency	60 Hz
Minimum Operating Frequency	50 Hz
Mounting Type	Surface
Number of Outputs	3
Number of Phases	3
Power Rating	1630 VA
Primary Current Rating	20 A
Primary Voltage Rating	415 V ac
Protection Features	Overload Protection
Secondary Voltage Rating	0 to 415 V ac, 0 to 470 V ac
Standards Met	RoHS Compliant
Termination Type	Termination Wire
Weight	50.1 kg
Width	300 mm