

## Datasheet

# RS Pro Insulated Crimp Spade Connector, 0.5mm<sup>2</sup> to 1.5mm<sup>2</sup>, 22AWG to 16AWG, M4 Stud Size, Red Vinyl

RS Stock No: 149-300



## Product Details

RS Pro insulated crimp spade connector in red vinyl colour, has 0.5 to 1.5 mm<sup>2</sup>, 22 to 16 AWG wire size and M4 stud size. This 15.5 mm connector has a PVC funnel entry range of crimps on reels. It is available in a variety of the most popular sizes.

## Features and Benefits

- PVC funnel entry range of crimps on reels
- Available in a variety of the most popular sizes
- Red 0.5 to 1.5 mm<sup>2</sup>, blue 1.5 to 2.5 mm<sup>2</sup> and yellow 4 to 6 mm<sup>2</sup>

**Specifications:**

Colour	Red
Contact Material	Copper
Contact Plating	Tin
Insulation	Insulated
Insulation Material	Vinyl
Maximum Wire Size (AWG)	16 AWG
Maximum Wire Size (mm <sup>2</sup> )	1.5 mm <sup>2</sup>
Minimum Wire Size (AWG)	22 AWG
Minimum Wire Size (mm <sup>2</sup> )	0.5 mm <sup>2</sup>
Overall Length	20.1 mm
Stud Size	M4.3
Thickness	0.8 mm
Width	7.2 mm
Wire Size	22 to 16 AWG
Current Rating	19 A
Temperature Rating	+75°C
Type	Flared Vinyl without Copper Sleeve
Voltage Rating	600 V