



ENGLISH

Datasheet

## RS Pro Steel Abrasive Circular Brush, 8000rpm, 100mm Diameter

RS Stock No: **291-3712**



### Product Details

RS Pro stainless steel abrasive circular brush has a diameter of 100 mm with a wire diameter of 0.30 mm. It comes with a arbour hole adaptor inserts. It is suitable for heavy duty applications such as descaling and deburring over large surface areas.

### Features and Benefits

- High quality industrial crimped filled materials
- 8000 rpm maximum safe speed
- Stainless steel bristle construction
- Arbor fixing type



ENGLISH

### Specifications:

Bristle Material	Steel
Fixing Type	Arbour
Bristle Length	23 mm
Diameter	100 mm
Fixing Size	20 mm
Maximum Safe Speed	8000 rpm
Suitable For	Heavy Duty Applications such as Descaling & Deburring over Large Surface Areas