

Datasheet

RS Pro Black CSAT ZH25 Self Amalgamating Tape

RS Stock No: **298-2049**



Product Details

RS Pro low smoke self-amalgamating tape in black colour, is a high performance ethylene propylene rubber tape for moisture sealing applications. The tape is specially formulated for low smoke and toxicity in fire. It offers excellent corona, UV and ozone resistance with excellent cold weather seal and corrosion protection. It measures 25 mm x 9 m. The tape is suitable for insulating cables, terminations and compression gland sealing.

Features and Benefits

- Specially formulated for low smoke and toxicity in fire (halogen free)
- Excellent corona, UV and ozone resistance
- Excellent temperature performance
- Suitable for use on voltage insulation up to 65 kV
- Self amalgamating
- Halogen free
- Easily applied - no tool or heat required
- Excellent cold weather seal and corrosion protection
- Over 3:1 stretch ratio
- Measures 25 mm x 9 m

**Specifications:**

Application	Busbar & Fitting Insulation, Cable Insulation, Protective Jacketing, Stable Packing Medium for Splices
Backing Material	EPDM
Colour	Black
Breakdown Voltage	65000 V
Length	9 m
Maximum Operating Temperature	+105°C
Minimum Operating Temperature	-55°C
Tensile Strength	2.5 MPa
Thickness	0.76 mm
Width	25 mm
Operating Temperature Range	-55 to +105°C