

Datasheet

RS Pro Steel Girder Suspension Clip & Hanger, 3 to 8 mm

RS Stock No: **277-389**



Product Details

RS Pro girder conduit clamp supports flange with thickness of 3 to 8 mm and pipe/conduit with diameter of 19 to 26 mm. This clamp made of steel, withstands 12 kg load.

Features and Benefits

- Either horizontal flange (H. flange) or vertical flange (V. flange)
- Clip-on conduit clip
- Steel construction
- Maximum load capacity is 12 kg



Specifications:

Flange Thickness Maximum	8 mm
Flange Thickness Minimum	3 mm
Flange Thickness	3 to 8 mm
Material	Steel
Maximum Load	12 kg
Pipe/Conduit Diameter Maximum	26 mm
Pipe/Conduit Diameter Minimum	19 mm
Pipe/Conduit Diameter	19 to 26 mm