

Datasheet

RS Pro Bright Zinc Plated Steel Nylon Insert Locking Nut, M6

RS Stock No: **275-614**



Product Details

RS Pro nylon insert locking nut made of bright zinc plated steel offers corrosion resistance. This nut is self locking due to glass filled nylon insert and features M6 metric internal threading to couple with threaded rod. The nut meets all the requirements of DIN6926 standards.

Features and Benefits

- Grade 8 steel, bright zinc plated
- M6 metric threading
- Plain faced flange
- Self-locking due to nylon insert
- To DIN6926

**Specifications:**

Finish	Bright Zinc Plated
Material	Steel
Thread Size	M6
Type	Nylon Insert
Flange Diameter	14.2 mm
Grade	8
Specification	DIN 6926
Thickness	8.74 to 9.1 mm
Thread Pitch	1
Width Across Flats	9.78 to 10 mm
Wrenching Height	5.7 mm