



ENGLISH

Datasheet

HSS PIPE REAMER TOOLS 10~34 MM

RS Stock number 456-901



Specification:

General purpose floor chisel - 57 mm HSS panel hole countersink head and P.P/TPR double injection grip

Finish:

Chemical black finish with machinery/grounding flute of pipe reamer tools head and P.P/TPR double injection grip

Contents:

1 pc - 10 ~ 34 mm high speed steel pipe reamer tools with red (P.P)/ black (TPR) double injection grip 6 step flutes, overall length - 160 mm