



ENGLISH

Datasheet

Rechargeable Battery Pack

RS Stock number: 777-0387

Dimensions(mm):



Specifications:

Model	HTD x 10	
Nominal Voltage	12 V	
Capacity	Typical	7000 mAh/0.2 CmA
	Minimum	6500 mAh/0.2 CmA
Charge	Standard	0.1 CmA for 16 hrs.
	Rapid	3 A for 3.6 hrs.(approx.) (With-ΔV, Temp., Time charging control)
	Trickle	0.03CmA (1 month)
Maximum Discharge Current	2 CmA (Continuous)	
Discharge Cut-off Voltage	10.0 V	
Applicable Temperature	Standard Charge	0~+70 °C
	Rapid Charge	0~+50 °C
	Discharge	-10~+70 °C
Storage	Within one year	-20 °C~+35 °C
	Within 3 months	-20 °C~+45 °C
	Within 1 month	-20 °C~+55 °C
Relative Humidity Range	65%±20%	
Weight	Approx. 1.4 Kg	