

Heavy Duty Mobile Steps - 4 Steps

RS Stock No. 412-034

Fully welded, tubular framed mobile safety steps.

These steps have a wide base for increased stability and non-slip rubber feet are fitted to the front legs as standard.

Both models come complete with rear fixed rubber wheels and rubber sprung swivel castors which lower to the ground under the operators weight.

Models have a double handrail.

Punched steel treads and platforms.

Epoxy powder coated red



The **5 tread model** is also fitted with a safety bar to prevent misuse of steps when mobile, and when released, this lowers the steps to the floor, enabling the operator to safely use the steps.



Product Description	Platform Height(mm)	Overall Size – H x W x D(mm)	Weight(Kgs)	Tread Size – W x D(mm)	Platform Tread Size – W x D(mm)	Castors	Wheels	RS Stock No.
4 Tread Steps	1000	1950 x 700 x 1100	32	450 x 200	450 x 400	75mmØ	160mmØ	412-034
5 Tread Steps	1250	2150 x 700 x 1200	42	550 x 200	550 x 400	75mmØ	160mmØ	412-024