



ENGLISH

Datasheet

**RS Pro Dial Thermometer, Centigrade, Fahrenheit Scale, 0 to +120 °C, 66mm dia. Dial**

RS Stock No: **431-5621**



## Product Details

RS Pro dial thermometer is designed to indicate surface temperature of pipework. It is suitable for boiler pipework, radiators and process pipelines.

## Features and Benefits

- Held in place by a wrap around spring
- No need to drill pipe work
- Acrylic window
- 66 mm diameter thermometer with Bi-metal movement



**Specifications:**

Application	Climate Control Technology
Best Accuracy	±4°C
Dial Diameter	66 mm
Maximum Temperature Measurement	+120°C
Temperature Scale	Centigrade, Fahrenheit
Thermometer Type	Dial
Temperature Range	0 to +120°C