

Datasheet

RS Pro Steel Zinc plated & clear Passivated Self-Clinching Captive Stud, M4, length-12mm

RS Stock No: **827-388**



Product Details

RS Pro self-clinching captive stud has zinc plated stainless steel construction and is clear passivated for corrosion resistance. This stud is designed for quick installation using a simple press. The stud measures 12 mm long and has M4 threads for a cost-effective means of threaded stud placement in thin sheet metal applications.

Features and Benefits

- Threaded self-clinching studs
- Designed for quick installation using a simple press
- Case-hardened, zinc plated and clear passivated mild steel, to BS3382
- Provides a cost-effective means of threaded stud placement in thin sheet metal applications

**Specifications:**

Finish	Zinc Plated, Clear Passivated
Fixing Hole Diameter	4 mm
For Panel Thickness Minimum	1 mm
Head Diameter	5.5 mm
Length	12 mm
Material	Steel
Thread Size	M4
Centre to Edge Distance	7 mm