



ENGLISH

Datasheet

Inspection Mirror Probe

RS Stock Number [471-8806](#)



Description:

An LED lamp consisting of a 350mm flexible, semi-rigid chrome-plated shank with threaded boss which retains any 1 of the 3 mirrors provided (14, 23 & 30mm dia. concave magnifying), all set on 25mm arm.

Designed for viewing inaccessible and poorly lit areas.

Powered by AA battery (not supplied).

Fitted Case supplied.

Magnetic pick-up Head:

Threaded chrome plated housing

12 mm diameter magnet

Recommended maximum load 250 g

Anodised Handle:

100 mm long by 25 mm diameter.

Holds 1 AA battery



ENGLISH

Illumination Switch:

Switch situated at end of handle.

Rubber Coated.

Positive click action ON/OFF.

Turn off lamp when not in use to conserve battery.