


**PIN OUT**



**NOTE 1:**

ITEM NO.	LENGTH
11. 99. 8946R	800 ± 20mm
11. 99. 8949R	1800 ± 30mm
11. 99. 8961R	3000 ± 50mm

**NOTE:**

- Electrical test:
  - 100% open short & miss wire test;
  - Insulation resistance:DC 300V 10M Ω ;
  - Contact resistance:5 Ω Max;
  - Dielectric strength:100V AC/Minute, 1mA.
- RoHS compliant
- PRINTING:USB 2.0 CABLE, 28AWG×1P+28AWG×2C
- Packing: 1PCS/PE BAG + LABEL 100PCS/CARTON

**MATERIAL LIST:**

④	OUTER MOLD	Shore 88A PVC(UL94V-2)color For White	2	
③	USB A TYPE	USB A /F Type, The Pin Gold Plating 30u", the shell for Nickel Plating	1	
②	USB A TYPE	USB A /M Type, The Pin Gold Plating 30u", the shell for Nickel Plating	1	
①	CABLE	USB 2.0 28AWG(7/0.12BC*1P)+28AWG(7/0.12BC*2C)+AEB B=0.12/3*16 AL-MG E=7/0.12BC JACKET:PVC/WHITE (WH11) OD: 3.8±0.2mm	1	
NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK



				REF.	ITEM NO. 11. 99. 8946 11. 99. 8961			
				PRODUCT NAME	USB 2.0 AM/AF		DRAW NO.	UNTT MM
		NEW		2009-11-20	A	DRAWNBY	CHECKBY	APPOBY DATE
BY	CHK	REVISION RECORD MODIFICATIONS		DATE	REV.	ALVAN	ALVAN	2009-11-20