



ENGLISH

Datasheet

**RS Pro Cutter 138 mm**

RS Stock No: **540-1969**



## Product Details

RS Pro cutter measuring 138 mm, cuts and bends the component lead in one action by allowing retention of the component in a PCB prior to soldering. The lead can be straightened and component removed if required. This special cutting and forming pliers has substantial pressed steel frames, chemically blackened, with return springs and plastic grips for easy, comfortable handling. The cutting edge is grounded to give precise cropping and manipulation of component leads. Tip is angled for easy access on to boards. The maximum cutting diameter of copper wire is 1 mm.

## Features and Benefits

- Tips are angled for easy access on to boards
- 138 mm long
- Return springs and plastic grips for easy and comfortable handling
- 1.02 mm maximum cutting capacity



ENGLISH

### Specifications:

Cutting Capacity Copper Wire	1.02 mm
ESD Safe	Yes
Maximum Cutting Capacity	1.02 mm
Overall Length	138 mm
Type	Cut & Bend