

Datasheet

## RS Pro Straining Screw, Jaw to Jaw, BSW 3/4

RS Stock No: 312-3500



### Product Details

RS Pro rigging screw with BSW 3/4 thread size, features jaw to jaw end fittings. This steel screw with galvanised finishing, has a working load limit of 22cwt.

### Features and Benefits

- Rigging screw tested and certified, fully galvanised
- Jaw to jaw end fittings
- BSW 3/4 thread size

**Specifications:**

Closed Length	387 mm
End A Fitting	Jaw
End B Fitting	Jaw
End Fittings	Jaw to Jaw
Eye Diameter	16 mm
Finish	Galvanised
Material	Steel
Open Length	550 mm
Thread Size	3/4 BSW
Weight	2.3 kg
Working Load Limit	22 cwt

diameter thread	length body	length closed position	length open position	diameter pin	length inside	opening jaw	width jaw	working load limit		weight each
a	b	c	d	e	f	g	h	tons	cwts	kg
inch	mm	mm	mm	mm	mm	mm	mm			
1/4	99	169	245	5	14	6	12		2	0.11
5/16	107	185	287	6	16	8	16		3	0.17
3/8	152	235	349	8	19	12	28		7.5	0.47
1/2	229	343	524	10	33	14	32		10	0.99
5/8	229	381	550	12	48	22	40		15	1.41
3/4	229	387	550	16	50	23	45		22	2.30
7/8	305	476	702	20	58	28	54		32	3.44
1	356	556	822	22	60	32	60		42	4.43
1.1/8	356	559	816	22	75	32	60	2	15	5.30
1.1/4	381	604	872	24	80	37	75	3	15	8.34
1.1/2	407	674	949	33	85	49	87	5	2	12.80
1.3/4	407	705	959	35	110	49	99	7		18.50
2	407	743	967	42	125	58	108	9	5	23.80
2.1/4	407	776	974	48	140	70	120	11	10	43.00
2.1/2	420	784	955	51	135	70	128	15		53.00

