

Datasheet

RS Pro 12 W LED Strip Light, T4, 230 V ac, Cool White, 7500K

RS Stock No: **720-3830**



Product Details

RS Pro 12 W LED strip light delivers colour temperature up to 7500K. The cool white light has a voltage rating of 230 V ac. This ultra-slim, low profile, linkable, low power LED strip lighting forms a direct replacement for your existing T4 fluorescent lighting. This light offers brilliant protection by using internal fuse.

Features and Benefits

- Low power consumption
- Up to 10 years continuous operation
- Cool running
- Integral on/off switch
- Internal fuse protection
- Easily "daisy chained" together using link cables

**Specifications:**

| | |
|-----------------------------|------------------|
| Colour Temperature | 7500 K |
| Depth | 44 mm |
| Diffuser Finish | Clear |
| Dimensions | 720 x 20 x 44 mm |
| Dimmable | No |
| EU Energy Efficiency Rating | A+ |
| Finish | White |
| Lamp Base | T4 |
| Lamp Supplied | Yes |
| Lamp Type | LED |
| Length | 720 mm |
| Light Colour | Cool White |
| Type | Strip Light |
| Voltage Rating | 230 V ac |
| Wattage | 12 W |
| Width | 20 mm |
| | |