

Datasheet

RS Pro 37 Way Right Angle Through Hole Mount PCB D-sub Connector Plug

RS Stock No: **437-5516**



Product Details

RS Pro D-sub connector plug has 90° mounting zinc passivated types with plastic feet for additional support. This right angle plug with 37 contacts has polyester housing. The through hole PCB mount plug has 5 A current rating and 750 V ac/dc voltage rating.

Features and Benefits

- Machined contacts
- 90° mounting zinc passivated types with plastic feet for additional support
- Male connector

Specifications:

Body Orientation	Right Angle
Contact Material	Copper Alloy
Contact Plating	Gold
Current Rating	5 A
Gender	Male
Housing Material	PET
Maximum Operating Temperature	+125°C
Minimum Operating Temperature	-55°C
Mounting Type	Through Hole
Number of Contacts	37
Voltage Rating	750 V ac/dc
Contact Resistance	5 mΩ
Insulation Material	Glass Filled PET
Insulation Resistance	5 x 10 ⁹ Ω
Shell Material	Steel
Shell Plating	Zinc