

Datasheet

RS Pro Straight 50 Ω Coaxial Adapter BNC Female to BNC Female 0 to 4GHz

RS Stock No: **546-3787**



Product Details

RS Pro straight BNC female to BNC female coaxial adapter comes with bayonet fixing and ABS insulation. It has a nickel plated body, nuts and washer and gold plated centre contact. It has 50 Ω impedance and operates at a frequency of 0 to 4 GHz. It measures 32.5 mm. This adapter is suitable for a variety of applications including video signalling and test equipment.

Features and Benefits

- BNC female to BNC female coaxial adapter
- Nickel plated body, nuts and washer and gold plated centre contact
- Suitable for a variety of applications including video signalling and test equipment

Specifications:

Adapter Type A	BNC
Adapter Type B	BNC
Adapter Type	BNC Socket to BNC Socket
Body Orientation	Straight
Body Plating	Nickel
Contact Material	Brass
Contact Plating	Gold
Gender A	Female
Gender B	Female
Impedance	50 Ω
Length	32.5 mm
Operating Frequency	0 to 4 GHz
Polarity	Normal
Body Material	Brass
Insulation Material	PTFE
Operating Temperature	-40 to +65°C
Voltage Rating	500 V