

Datasheet

RS Pro Straight 50 Ω Cable Mount BNC Connector Plug, Crimp Termination RG58 Nickel

RS Stock No: **546-4853**



Product Details

RS Pro straight cable mount BNC connector plug features a nickel plated body with gold and copper contacts. This male connector plug has 50 Ω impedance. It is suitable for a variety of applications including video signalling and test equipment.

Features and Benefits

- Nickel plated body with gold and copper contacts
- Crimp termination method
- Male connector

**Specifications:**

Body Orientation	Straight
Body Plating	Nickel
Cable Type	RG58
Contact Material	Copper
Contact Plating	Gold
Gender	Male
Impedance	50 Ω
Mounting Type	Cable Mount
Operating Frequency	4 GHz
Polarity	Normal
Termination Method	Crimp
Body Material	Brass
Insulation Material	PTFE
Operating Temperature Range	-20 to +60°C
Standards Met	RoHS Compliant
Voltage Rating	500 V (Working)