

Datasheet

RS Pro Digital & Programmable HVAC Thermostat with LCD Display

RS Stock No: **823-4936**



Product Details

RS Pro digital and programmable HVAC thermostat comes with LCD display for effective measurements. It is suitable for operating temperatures ranging from +5 to +35°C. This device features economic and comfort mode. It includes compressor delay option for cooling selection.

Features and Benefits

- Optional economic operation or comfort operation by switch
- Transmitter power has battery back-up; the receiver can bear 16 A current voltage
- Individual RF ADDRESS CODE to avoid interference
- Room temperature easy read out by Mini LCD display, without backlight saves energy
- The big control knob is easy to understand and adjust
- Optional temperature display of Celsius or Fahrenheit scale
- Compressor delay option for cooling selection
- Low battery indication
- Power source Control Centre 2 AA batteries (Not Supplied)
- Receiver of 230 V ac±10 A 50/60 Hz



Specifications:

Additional Features	LCD Display
Contact Rating	10 A
Contact Voltage	230 V ac
Maximum Temperature	+35°C
Minimum Temperature	+5°C
Supply Voltage	230 V ac
Temperature Range	+5 to +35°C