

## Datasheet

**RS 2 Core Unscreened Industrial Cable, PVC Sheath, 5.9mm OD, 0.5 mm<sup>2</sup> CSA 2.5 A, 440 V, 100m**

**Stock Number - 660-4080**



### Description:

**Rated Temperature (oC): -20 ~ 80**

**Rated Voltage (V):440**

**Flammability Test: IEC60332-1**



**Construction:**

Conductor: Tinned Copper

Conductor Dia. (mm):  $0.20 \pm 0.008 \times 16$

Insulation: PVC

Insulation Dia. (mm):  $1.8 \pm 0.05 \times 2C$

Tape: Mylar Spiral

Coverage:  $\geq 115\%$

ID Thread : Green, White/Green

A rip cord : 210 D

Jacket: FR-PVC

Outer Dia. (mm):  $5.5 \pm 0.1$

**Colour:**

The colour of the insulation: Red , Blue , Green ,  
Yellow ,

White , Black , Brown , Violet , Orange , Pink , Light  
Green ,

Grey , Red/Blue , Green/Red , Yellow/Red ,  
White/Red ,

Red/Black , Red/Brown , Yellow/Blue , White/Blue ,

The jacket colour: Black

Marking(3times/m):

RS 6600476 7 - 2 - 20C



ENGLISH

Max. Conductor DC Resistance at 20°C (  $\Omega$ /Km ) :  
<40

Min. Insulation DC Resistance at 20°C (  $M\Omega$ \*KM ) :  
>200

Current Rating : 2.5 A

