



ENGLISH

Datasheet

RS Pro 8mm probe Inspection Camera Kit, 880mm Probe Length, LED Illumination

RS Stock No: **847-8956**



Product Details

RS Pro 8 mm probe inspection camera kit features professional and high quality video boroscope that makes it easy to inspect hard to reach and hard to see areas and equipment. Excellent for automotive applications, i.e. internal inspections and reading stamped identifications etc.

Features and Benefits

- 1/9 Inch VGA CMOS sensor with 640 x 480 pixel resolution
- Lens outer diameter of 8 mm
- Flexible gooseneck outer diameter of 6.5 mm
- Waterproof IP67
- Upside down screen function
- Conveniently powered by AA batteries
- Great design with up to x4 zoom function
- Interchangeable/extendable lens
- Carry hook in handle
- Rigid carry case, snap on hook, magnet and mirror attachments



Specifications:

Battery Type	AA
Field of View	54°
Illumination Type	LED
Maximum Bending Radius	45 mm
Probe Diameter	8 mm
Probe Length	880 mm
Resolution	960 x 240 pixels
Operating Temperature Range	0 to +45°C
Standards Met	CE Certified