

MR16 LED 12V AC/DC

■ GU5,3 LED - non dimmable / not dimmable

CODE	REF.	W		Lm	Cd	°	°K	ENERGY LABEL	N°
▶ Ø 50 mm X h 47 mm - 12V AC/DC IRC > 80									
180576	LE 1311 NW	3,6	20	240	550	36	3000	A+	1
180577	LE 1313 NW	5,5	35	345	800	36	3000	A+	2
▶ Ø 50 mm X h 45 mm - 12V AC/DC IRC > 80									
180635	LE 1334 NW	6,8	60	435	1040	36	3000	A+	3
180636	LE 1334 CW	6,8	60	435	1040	36	5000	A+	3
▶ Ø 50 mm X h 53 mm - 12V AC/DC IRC > 80									
180598	LE 1420 NW	8	50	520	1380	36	3000	A+	4



1



2



3



4

■ GU5,3 LED - dimmable / dimmable

CODE	REF.	W		Lm	Cd	°	°K	ENERGY LABEL
▶ Ø 50mm X h 50mm - 12V AC/DC IRC > 80								
180611	LE 1422 NW	8,5	50	600	1275	40	3000	A



■ GU5,3 LED COB / COB type

CODE	REF.	W		Lm	Cd	°	°K	ENERGY LABEL	N°
▶ Ø 50mm X h 46mm - 12V AC/DC IRC > 80									
180660	LE 1314 NW	5	37	310	810	30	3000	A+	1
180666	LE 1312 WW	5,5	-	450	-	36	2700	A+	2



1



2

■ GU5,3 MR16 STANDARD - 20 LED - non dimmable / not dimmable

CODE	REF.	W	Lm	Cd	°	ENERGY LABEL	
▶ Ø 50 mm X h 49 mm - 12V AC - 1,18 W							
180156	LE 1011 R	1,18	4	50	15	A	Rouge/Red
180157	LE 1011 G	1,18	4	50	15	A	Vert/Green
180158	LE 1011 B	1,18	6	100	15	A	Bleu/Blue
180160	LE 1011 W	1,4	43	290	17	A+	Blanc/White 6500°K

