

General Information

| | |
|-------------------------------|---|
| Extended Product Type: | BJH14-2 |
| Product ID: | 1SNA173438R2400 |
| EAN: | 3472591734386 |
| Catalog Description: | BJH14-2 Jumper Bars |
| Long Description: | - Not assembled screw jumpers bar, - Allows connection between consecutive blocks, - Perforated jumper bar without captive screw and washer, - The perforated jumper bar must be fitted under the washer and the nut of each block. |

Additional Information

| | |
|---|--|
| ABB Industrial IT Suite: | Control IT |
| Ambient Air Temperature: | Operation -55 ... +110 °C |
| Color: | Grey |
| Country of Origin: | France (FR) |
| Customs Tariff Number: | 85389099 |
| Data Sheet, Technical Information: | 1SNC160001C0207-CH-J Accessories |
| Degree of Protection: | acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20 |
| EAN: | 3472591734386 |
| ETIM 4: | EC000489 - Cross-connector for terminal block |
| ETIM 5: | EC000489 - Cross-connector for terminal block |
| ETIM 6: | EC000489 - Cross-connector for terminal block |
| Function: | Jumper Bars |
| IT Publishing Status: | Level 0 - Information enabled |
| Industrial IT Certification Level: | 0 |
| Instructions and Manuals: | 1SNC160001C0207-CH-J Accessories |
| Invoice Description: | BJH14-2 Jumper Bars |
| Minimum Order Quantity: | 10 piece |
| Mounting on DIN Rail: | G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 |
| Object Classification Code: | X |
| Order Multiple: | 10 piece |
| Package Level 1 EAN: | 3472591734386 |
| Package Level 1 Gross Weight: | 0.053 kg |
| Package Level 1 Units: | 10 piece |
| Package Level 2 Units: | 200 piece |
| Product Main Type: | BJH |
| Product Name: | Jumper Bar |
| Product Net Depth: | 12 mm |
| Product Net Height: | 2 mm |
| Product Net Weight: | 5.3 g |
| Product Net Width: | 14 mm |
| Selling Unit of Measure: | piece |
| Spacing: | 14 mm |
| Sub-Function: | Not assembled screw jumpers bar |
| Suitable For: | HD16/14.FF5 |

