



## LIQUIfit Pressure & Temperature

Ø	T°		
	-10°C --> +40°C -14°F --> +104°F -263°K --> +313°K	+40°C --> +65°C +104°F --> +149°F +313°K --> +338°K	+65°C --> +95°C +149°F --> +203°F +338°K --> +368°K
4 - 6 - 8 mm 5/32 - 1/4 - 5/16	16 bar	10 bar	4 bar
10 mm - 3/8	13 bar	7 bar	4 bar
12 mm - 1/2	11 bar	7 bar	4 bar