



ENGLISH

Datasheet

RS Pro Halogen Machine Light, 24 Volts, 70 W, Adjustable Arm, 830mm Reach, 830mm Arm Length

RS Stock No: **433-3051**



Product Details

RS Pro halogen machine light features an IP65 rated, totally enclosed lamp head, which provides protection against dust, coolants and swarf. It has a voltage rating of 24 V and power rating of 70 W.

Features and Benefits

- High power halogen machine lights for industrial use, ideal for use in fixed positions
- Diecast head protected to IP65
- Reinforced glass cover
- Fitted with anti-glare louvre
- On/off switch on head along with adjusting handle
- Fitted with a 1.8 m lead without plug



Specifications:

Arm Length	830 mm
Arm Type	Adjustable
Cable Length	1.8 m
EU Energy Efficiency Rating	C
IP Rating	IP65
Lamp Supplied	Yes
Lamp Type	Halogen
Maximum Reach	830 mm
Voltage Rating	24 V
Wattage	70 W