



Datasheet

ENGLISH

RS Pro Nitrile Rubber O-Ring Cord



Description:

The O-Ring is a simple, versatile and economical device with a vast range of uses. The most common of these are as a static seal replacing a gasket or sealing washer. It can be used to seal radially in both internal and external positions and axially on its face.

Specifications:

RS Stock No	Description	Diameter	Length	Material
138-1599	O-Ring Cord, Dia. 1.78mm x 8.5m	1.78 mm	8.5 Metres	Nitrile Rubber
138-1600	O-Ring Cord, Dia. 2mm x 8.5m	2.0 mm	8.5 Metres	Nitrile Rubber
138-1601	O-Ring Cord, Dia. 2.62mm x 8.5m	2.62 mm	8.5 Metres	Nitrile Rubber
138-1602	O-Ring Cord, Dia. 3.5mm x 8.5m	3.5 mm	8.5 Metres	Nitrile Rubber
138-1604	O-Ring Cord, Dia. 4.0mm x 8.5m	4.0 mm	8.5 Metres	Nitrile Rubber
138-1605	O-Ring Cord, Dia. 4.5mm x 8.5m	4.5 mm	8.5 Metres	Nitrile Rubber
138-1606	O-Ring Cord, Dia. 5mm x 8.5m	5.0 mm	8.5 Metres	Nitrile Rubber
138-1607	O-Ring Cord, Dia. 5.33mm x 8.5m	5.33 mm	8.5 Metres	Nitrile Rubber
138-1608	O-Ring Cord, Dia. 6mm x 8.5m	6.0 mm	8.5 Metres	Nitrile Rubber
138-1609	O-Ring Cord, Dia. 7mm x 8.5m	7.0 mm	8.5 Metres	Nitrile Rubber
138-1610	O-Ring Cord, Dia. 8mm x 8.5m	8.0 mm	8.5 Metres	Nitrile Rubber