



ZARGES

Datasheet

Zarges 5 Tread Double-Sided 'R13' Stepladder

Stock Code. 172-1310

Specification

Aluminium stiles

Aluminium treads with R13 surface



Standard

New EN131 Professional
150KG Rating

RS Code	Zarges Code	Overall Length (m)	Vertical Height (m)	Working Height Approx. (m)	No. of Treads	Weight (KG)
172-1310	41553	1.42	1.32	2.80	2 x 5	8.40

Features:

The ladder with the highest non-slip performance thanks to R13 treads for oily and wet conditions.

80 mm deep treads with R13 surface and perforations to drain fast.

Abrasion-resistant, anodised stiles.

Maximum working heights thanks to 280mm high access.

Hinges of diecast aluminium.

Replaceable 2-component plastic end caps ensure positioning without risk of slipping and at the same time provide firm seating in the stile.

High-strength perlon belts prevent splay.