



ENGLISH

Datasheet

Stock No: 161-1530

RS Pro Multimeter Fuse, 500mA 1000V



Product Details

RS Pro Replacement Fuses for Fused Test Leads & Accessories

Pack of 3 replacement fuses for RS Pro GS38 fused test leads and fused accessories. High Breaking Capacity rated at 500 mA with 50 kA rupture current.

Size:- 6.3mm x 32mm

Replacement fuse for fused test leads including RS kits:-

204-583, 204-599, 125-3731, 125-3732, 125-3734, 212-966 & 731-5273

Specification

Voltage:	1000 Volts AC & DC
Current Rating:	500 mA
Safety Category Voltage:	1000 Volts
Safety Category Level:	CAT IV
Minimum Operating Temperature:	-20°C
Maximum Operating Temperature:	+70°C