



ENGLISH

Datasheet

RS Pro NiMH AA Rechargeable Battery, 2600mAh

RS Stock No: **617-0795**



Product Details

RS Pro Ni-MH AA battery has a storage capacity of 2600 mAh. This 1.2 V rechargeable battery offers quick charging rate of 4 - 6 hours. The tagging allows for easy combining into larger battery packs for permanent installation.

Features and Benefits

- Voltage 1.2 V
- Quick 4 to 6 hours charging rate
- 2600 mAh capacity

**Specifications:**

Chemistry	NiMH
Size	AA
Terminal Type	Tagged
Capacity	2600 mAh
Dimensions	14.3 x 50.5 mm
Maximum Continuous Current	1 mA
Maximum Operating Temperature	+60°C
Minimum Operating Temperature	-10°C
Nominal Voltage	1.2 V
Open Circuit Voltage	1.31 V
Operating Temperature Range	-10 to +60°C
Size	AA
Weight	30 g