

02 02 180

High Leverage Combination Pliers



- 35 % less effort required than with conventional combination pliers
- With cutting edges (hardness approx. 63 HRC) for heavy duty
- Easier work due to optimised leverage
- Easier cutting, powerful gripping, bending and pulling
- Long cutting edges for thicker cables
- With gripping zones for flat and round material, suitable for versatile use
- High-grade special tool steel, forged, multi stage oil-hardened



Article No.	02 02 180
EAN	4003773010517
Pliers	black atramentized
Head	polished
Handles	with multi-component grips
Cutting capacities hard wire (diameter) Ø mm	2,5
Cutting capacities piano wire (diameter) Ø mm	2,0
Cutting capacity copper cable, multiple-stranded (diameter) Ø mm	11,5
Cutting capacity copper cable, multiple-stranded mm²	16
Length mm	180
Net weight g	240



technical change and errors excepted

