

74 02 160

High Leverage Diagonal Cutter



- For very tough, continuous use
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Precision cutting edges additionally induction hardened (cutting edge hardness approx. 64 HRC), for all sorts of wire including piano wire
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



20 % less effort required

compared to conventional diagonal cutters of the same length.

With integrated forged joint axle.

Article No.	74 02 160
EAN	4003773011873
Pliers	black atramentized
Head	polished
Handles	with multi-component grips
Style	0
Cutting capacities medium hard wire (diameter) Ø mm	3,4
Cutting capacities hard wire (diameter) Ø mm	2,5
Cutting capacities piano wire (diameter) Ø mm	2,0
Length mm	160
Net weight g	209



technical change and errors excepted

