



mecalelectro

Solenoid Latching – 8.MB5.02.29



Stroke: 20 mm

Force at beginning of stroke (FM: 100/40//25/5%): 1/4/10/20 N

Holding force power off: 60 N

Power Consumption (FM: 100/40/25/5%): 20/40/80/200 W

Total mass: 550 g

Degree of protection / Energetic class: IP 40 / B

Standard supplies: 24Vcc

Possibles supplies: From 6 to 240Vcc

Pulse duration: 100 à 150

Standard: NF C 79300

Examples of applications: various automations, multiple locks